

**B 50500** similar to ISO 7380

**Safety screws**

Linsenkopf | Torx mit Zapfen

Stainless steel A2 | Cr(VI)-free | Metric thread



Diameter (d)	d <sub>1</sub>		k		r	s		t		
	min.	max.	min.	max.	nominal size	nominal size	min.	max.	max.	min.
4	7.24	7.6	1.95	2.20	4.1	2.5	2.52	2.58	1.55	1.30
5	9.14	9.5	2.50	2.75	5.2	3.0	3.02	3.08	2.12	1.56
6	10.07	10.5	3.00	3.30	5.6	4.0	4.02	4.10	2.26	2.08
8	13.57	14.0	4.10	4.40	7.5	5.0	5.02	5.14	3.05	2.60

Length (l) nominal size
10
12
16
20
25
30

Length (l) nominal size
40
45
50

Diameter (d)	Length (l)								
	10	12	16	20	25	30	40	45	50
4		●	●	●		●			
5	●	●	●	●	●	●			
6	●		●	●	●	●		●	●
8		●	●				●		●

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

