

B 51010

Insert nuts

Regular collar

Steel | zinc-plated, thick-film passivated (VZD) | Cr(VI)-free | Metric thread



Diameter (d)	d ₁		d ₂			d ₃		h ₁		
	min.	max.	nominal size	min.	max.	min.	max.	nominal size	min.	max.
M3	4.42	4.5	4.7	4.65	4.72	4.4	4.5	0.9	0.85	0.97
M4	5.42	5.5	5.7	5.65	5.72	5.4	5.5	0.9	0.85	0.97
M5	6.42	6.5	6.75	6.69	6.80	6.4	6.5	0.9	0.85	0.97
M6	7.92	8.0	8.3	8.24	8.35	7.8	8.0	0.9	0.85	0.97
M8	9.90	10.0	10.3	10.24	10.35	9.8	10.0	1.9	1.70	1.95
M10	12.40	12.5	12.85	12.78	12.90	12.3	12.5	1.9	1.70	1.95
M12	14.40	14.5	14.85	14.76	14.90	14.3	14.5	2.9	2.60	2.95
M16	18.30	18.5	18.85	18.75	18.90	18.3	18.5	2.4	2.00	2.45

Diameter (d)	h ₂		h		s nominal size	Pitch (P)	Tool size
	nominal size	min.	min.	max.			
M3	0.4	0.6	2.80	3.0	5.5	0.50	SW 5,5
M4	0.4	0.6	3.00	3.2	7.0	0.70	SW 7
M5	0.4	0.6	3.80	4.0	8.0	0.80	SW 8
M6	0.4	0.6	4.64	5.0	10.0	1.00	SW 10
M8	–	0.6	6.14	6.5	13.0	1.25	SW 13
M10	–	0.6	7.64	8.0	15.0	1.50	SW 15
M12	–	0.6	9.58	10.0	17.0	1.75	SW 17
M16	–	0.6	12.58	13.0	22.0	2.00	SW 22

All technical data refer to the measure mm

