

**DIN 1** similar to ISO 2339

# Taper pins

Form B

Stainless steel 1.4305 | Cr(VI)-free

Further information: DIN-standard has been withdrawn | nominal lengths changed



| Diameter<br>(d) | d <sub>1</sub><br>nominal size | r    |
|-----------------|--------------------------------|------|
| 1               | 1                              | 1.0  |
| 1.5             | 1.5                            | 1.6  |
| 2               | 2                              | 2.5  |
| 2.5             | 2.5                            | 2.5  |
| 3               | 3                              | 4.0  |
| 4               | 4                              | 4.0  |
| 5               | 5                              | 6.0  |
| 6               | 6                              | 6.0  |
| 8               | 8                              | 10.0 |
| 10              | 10                             | 10.0 |

| Length (l)<br>nominal size |
|----------------------------|
| 8                          |
| 10                         |
| 12                         |
| 14                         |
| 16                         |
| 18                         |
| 20                         |
| 22                         |
| 24                         |
| 26                         |
| 28                         |
| 30                         |

| Length (l)<br>nominal size |
|----------------------------|
| 32                         |
| 36                         |
| 40                         |
| 45                         |
| 50                         |
| 55                         |
| 60                         |
| 70                         |
| 80                         |
| 90                         |
| 100                        |
| 120                        |

All technical data refer to the measure mm



**DIN 1** similar to ISO 2339

# Taper pins

Form B

Stainless steel 1.4305 | Cr(VI)-free

| Diameter<br>(d) | Length (l) |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |     |   |
|-----------------|------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|-----|-----|---|
|                 | 8          | 10 | 12 | 14 | 16 | 18 | 20 | 22 | 24 | 26 | 28 | 30 | 32 | 36 | 40 | 45 | 50 | 55 | 60 | 70 | 80 | 90 | 100 | 120 |   |
| 1               |            | ●  | ●  | ●  | ●  | ●  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |     |   |
| 1.5             | ●          |    | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  |    |    |    |    |    |    |    |    |    |    |    |    |     |     |   |
| 2               |            | ●  |    | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  |    |    |    |    |    |    |    |    |    |     |     |   |
| 2.5             |            |    | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  |    |    |    |    |    |    |    |    |    |     |     |   |
| 3               |            |    |    | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  |    |    | ●  | ●  |    |    |    |    |    |     |     |   |
| 4               |            |    |    |    | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  |    |    |    |     |     |   |
| 5               |            |    |    |    | ●  |    | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  |    |    | ●  | ●  |    |    | ●  |    |     |     |   |
| 6               |            |    |    |    |    |    |    |    | ●  | ●  | ●  | ●  | ●  | ●  |    |    | ●  | ●  | ●  | ●  | ●  | ●  | ●   | ●   | ● |
| 8               |            |    |    |    |    |    |    |    |    |    | ●  |    | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●   | ●   | ● |
| 10              |            |    |    |    |    |    |    |    |    |    |    |    | ●  | ●  | ●  | ●  |    | ●  | ●  |    | ●  | ●  | ●   |     |   |

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

