


**DIN 7985** similar to ISO 7045

## Pan head screws

Cross-slot phillips

Stainless steel A4 | Cr(VI)-free | Metric thread

Further information: DIN-standard has been withdrawn | changed head height



Diameter (d)	a max.	da max.	dk		nominal size	k		rf	r max.	Pitch (P)	v	Tool size
			min.	max.		min.	max.					
M2	0.8	2.6	3.70	4	1.6	1.48	1.72	4	0.10	0.40	1.1	H1
M2.5	0.9	3.1	4.70	5	2.0	1.88	2.12	5	0.10	0.45	1.3	H1
M3	1.0	3.6	5.70	6	2.4	2.28	2.52	6	0.10	0.50	1.6	H1
M4	1.4	4.7	7.64	8	3.1	2.95	3.25	8	0.20	0.70	2.0	H2
M5	1.6	5.7	9.64	10	3.8	3.65	3.95	10	0.20	0.80	2.5	H2
M6	2.0	6.8	11.57	12	4.6	4.45	4.75	12	0.25	1.00	3.0	H3
M8	2.5	9.2	15.57	16	6.0	5.85	6.15	16	0.40	1.25	3.7	H4

nominal size	Length (l)	
	min.	max.
3	2.80	3.20
4	3.75	4.25
5	4.75	5.25
6	5.75	6.25
8	7.70	8.30
10	9.70	10.30
12	11.65	12.35
14	13.65	14.35
16	15.65	16.35
18	17.65	18.35

nominal size	Length (l)	
	min.	max.
20	19.60	20.40
25	24.60	25.40
30	29.60	30.40
35	34.50	35.50
40	39.50	40.50
45	44.50	45.50
50	49.50	50.50
60	59.00	61.00

All technical data refer to the measure mm



**DIN 7985** similar to ISO 7045

## Pan head screws

Cross-slot phillips

Stainless steel A4 | Cr(VI)-free | Metric thread

Diameter (d)	Length (l)																	
	3	4	5	6	8	10	12	14	16	18	20	25	30	35	40	45	50	60
M2	●	●	●	●	●	●	●	●	●	●	●							
M2.5		●	●	●	●	●	●	●	●	●	●	●	●					
M3		●	●	●	●	●	●	●	●	●	●	●	●	●				
M4			●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
M5				●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
M6					●	●	●		●		●	●	●	●	●	●	●	●
M8																		●

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

