

DIN 933 similar to ISO 4017


Hexagon head bolts

Hexagon head | external hex | fully threaded

Steel 5.6 | bright | Cr(VI)-free | Metric thread

Further information: DIN-standard has been withdrawn | changed spanner widths for M10, M12, M14 and M22 | screws can be paired with a 6h tolerance-compliant female thread

There is a separation into product classes A and B, with the data sheet showing the largest range of values. For more information, see the technical details of the selected article.



Diameter (d)	a		c		d _a	d _w	e	k		r	s		Pitch (P)	Tool size	
	max.	min.	max.	min.	max.	min.	min.	nominal size	min.	max.	min.	max.			
M6	3.00	0.15	0.5	0.6	6.8	8.7	10.89	4.0	3.76	4.24	0.25	10	9.64	1.00	SW 10
M8	3.75	0.15	0.6	0.6	9.2	11.4	14.20	5.3	5.06	5.54	0.40	13	12.57	1.25	SW 13
M10	4.50	0.15	0.6	0.6	11.2	15.4	18.72	6.4	6.11	6.69	0.40	17	16.57	1.50	SW 17
M12	5.25	0.15	0.6	0.6	13.7	17.2	20.88	7.5	7.21	7.79	0.60	19	18.48	1.75	SW 19
M16	6.00	0.20	0.8	0.8	17.7	22.0	26.17	10.0	9.71	10.29	0.60	24	23.16	2.00	SW 24
M20	7.50	0.20	0.8	0.8	22.4	27.7	32.95	12.5	12.15	12.85	0.80	30	29.16	2.50	SW 30
M24	9.00	0.20	0.8	0.8	26.4	33.2	39.55	15.0	14.65	15.35	0.80	36	35.00	3.00	SW 36
M27	9.00	0.20	0.8	0.8	30.4	38.0	45.20	17.0	16.65	17.35	1.00	41	40.00	3.00	SW 41
M30	10.50	0.20	0.8	0.8	33.4	42.7	50.85	18.7	18.28	19.12	1.00	46	45.00	3.50	SW 46
M33	10.50	0.20	0.8	0.8	36.4	46.5	55.37	21.0	20.68	21.42	1.00	50	49.00	3.50	SW 50
M36	12.00	0.20	0.8	0.8	39.4	51.1	60.79	22.5	22.08	22.92	1.00	55	53.80	4.00	SW 55

nominal size	Length (l)	
	min.	max.
10	9.71	10.29
12	11.65	12.35
16	15.65	16.35
20	19.58	20.42
25	23.95	26.05
30	28.95	31.05

nominal size	Length (l)	
	min.	max.
35	33.75	36.25
40	38.75	41.25
45	43.75	46.25
50	48.75	51.25
55	53.50	56.50
60	58.50	61.50

nominal size	Length (l)	
	min.	max.
65	63.50	66.50
70	68.50	71.50
75	73.50	76.50
80	78.50	81.50
90	88.25	91.75
100	98.25	101.75

All technical data refer to the measure mm



DIN 933 similar to ISO 4017

Hexagon head bolts

Hexagon head | external hex | fully threaded

Steel 5.6 | bright | Cr(VI)-free | Metric thread

Diameter (d)	Length (l)																	
	10	12	16	20	25	30	35	40	45	50	55	60	65	70	75	80	90	100
M6	●	●	●	●	●	●	●	●										
M8		●	●	●	●	●	●	●	●									
M10			●	●	●	●	●	●	●									
M12				●	●	●	●	●	●	●	●	●						
M16					●	●	●	●		●	●	●	●	●	●			
M20							●	●		●	●	●	●	●	●	●		
M24										●	●		●	●	●		●	
M27												●	●	●	●	●	●	●
M30												●		●	●	●	●	
M33												●		●		●		
M36												●		●		●	●	●

● Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

