


DIN 982 similar to ISO 7040

Hexagon nuts

With clamping part | non-metallic insert | high form

Steel 8 | zinc-plated, thick-film passivated (VZD)

Further information: DIN standard has been withdrawn | modified nut height and wrench width



Diameter (d)	d _a		h		e	m	s		Pitch (P)	Tool size
	min.	max.	min.	max.			min.	max.		
M5	5	5.75	6.00	6.3	8.79	4.40	7.78	8	0.80	SW 8
M6	6	6.75	7.70	8.0	11.05	4.90	9.78	10	1.00	SW 10
M8	8	8.75	9.14	9.5	14.38	6.44	12.73	13	1.25	SW 13
M10	10	10.80	11.14	11.5	18.90	8.04	16.73	17	1.50	SW 17
M12	12	13.00	13.64	14.0	21.10	10.37	18.67	19	1.75	SW 19
M20	20	21.60	20.70	22.0	32.95	16.90	29.16	30	2.50	SW 30

All technical data refer to the measure mm

