

**E 5411**

**EJOT®-Delta PT-screws**

Raised countersunk head with pressed-on washer | torx plus /autosert drive

Steel 10 | zinc-plated | Cr(VI)-free | Self-tapping thread

Further information: For further information and CAD-files please follow the link to the

EJOT-homepage:

<http://www.ejot.com/industry>

Diameter (d)	r nominal size	s nominal size	Pitch (P)	t		K	Tool size
				max.	min.		
2.2	0.35	0.6	0.85	1.14	0.68	1.6	1
2.5	0.4	0.7	0.95	1.28	0.82	1.8	1
4	0.6	1.0	1.46	1.96	1.33	2.5	2

Length (l) nominal size
6
9
12

Diameter (d)	Length (l)		
	6	9	12
2.2	●		
2.5			●
4		●	

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

