

E 5412

EJOT®-Delta PT-screws

Raised countersunk head with pressed-on washer | torx plus /autosert drive

Steel 10 | Cr(VI)-free | Self-tapping thread

Further information: For further information and CAD-files please follow the link to the EJOT-homepage:

<http://www.ejot.com/industry>

Diameter (d)	m nominal size	r nominal size	Pitch (P)	t		K	Tool size
				max.	min.		
2.5	2.59	0.4	0.95	1.33	1.08	1.9	1
3.5	3.93	0.5	1.29	1.72	1.26	2.7	2
4	4.29	0.6	1.46	2.08	1.62	3.1	2

Length (l) nominal size
8
12
35

Diameter (d)	Length (l)		
	8	12	35
2.5	●		
3.5			●
4	●	●	

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

