

**E 5452**

**EJOT®-Delta PT-screws**

Raised countersunk head with pressed-on washer | torx plus /autosert drive

Stainless steel A2 | Cr(VI)-free | Self-tapping thread

Further information: For further information and CAD-files please follow the link to the EJOT-homepage:

<http://www.ejot.com/industry>

Diameter (d)	d <sub>1</sub> nominal size	r max.	Pitch (P)	t		Tool size
				max.	min.	
2	2	0.35	0.78	0.85	0.65	T6 (1,75)
2.2	2.2	0.35	0.85	0.85	0.65	T6 (1,75)
2.5	2.5	0.40	0.95	1.00	0.80	T8 (2,4)
3	3	0.50	1.12	1.30	1.00	T10 (2,8)
3.5	3.5	0.50	1.29	1.50	1.00	T15 (3,35)
4	4	0.60	1.46	1.80	1.40	T20 (3,95)
4.5	4.5	0.60	1.63	1.80	1.40	T20 (3,95)
5	5	0.70	1.80	1.90	1.50	T25 (4,5)

Length (l) nominal size
4.5
5.0
7.0
8.0
9.0
10.0
12.0
14.0

Length (l) nominal size
16.0
18.0
20.0
24.0
25.0
30.0
35.0

Diameter (d)	Length (l)														
	4.5	5	7	8	9	10	12	14	16	18	20	24	25	30	35
2			●				●	●		●					
2.2	●	●		●											
2.5						●	●								
3				●	●	●	●		●	●			●		●
3.5										●					
4				●		●	●	●			●	●			
4.5						●									
5						●								●	

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

