

ISO 7380-2

Round head screws

Halbrundkopf mit Flansch | Torx

Steel 10.9 | zinc-plated, thick-film passivated (VZD) | Cr(VI)-free | Metric thread



Diameter (d)	b nominal size	c		d _a max.	d _c		d _k		d _s	
		min.	max.		min.	max.	min.	max.	min.	max.
5	22	0.80	1.0	5.7	11.10	11.8	8.4	8.8	4.82	5
8	28	1.25	1.5	9.2	17.10	17.8	12.8	13.2	7.78	8
10	32	1.70	2.0	11.2	21.06	21.9	16.1	16.5	9.78	10

Diameter (d)	d _w min.	k		e min.	s		Pitch (P)	w min.	
		min.	max.		nominal size	min.			max.
5	10.40	2.5	2.75	3.44	5	5.02	5.14	0.80	0.38
8	16.40	4.1	4.40	5.72	5	5.02	5.14	1.25	1.05
10	20.22	5.2	5.50	6.86	6	6.02	6.14	1.50	1.45

Length (l) nominal size
8
20
30

Diameter (d)	Length (l)		
	8	20	30
5	●		
8			●
10		●	

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

