All technical data refer to the measure mm


RIVKLE® Mandrel


Spare threaded mandrel for the RIVKLE® ES 51 hydraulic manual setting tool.

Technical information can be found on the last page.




Diameter	Article number	For
(d)		tool type
M 6	23510806020	ES 51
M 8	23510808020	ES 51
M 10	23510810020	ES 51
M 12	23510812020	ES 51
M 14	23510814020	ES 51






Grip range

Defines the range of total thickness of the customers part (even if it consists of more than one layer)



Hole geometry

If round -> diameter If hexagonal -> wigth across flats



Difference of total length before and after installation



in accordance to chosen RIVKLE®

