RIVKLE[®] Nose piece

For blind rivet studs and riveting forces > 18 kN (M8 and M10).

Technical information can be found on the last page.





Diameter	Article number	For
(d)		tool type
M3 - M8	23615700309	P1007



Böllhoff Group · Archimedesstr. 1-4 · 33649 Bielefeld · Phone: +49 521 4482-1387 · fat@boellhoff.com · eshop.boellhoff.de/en/home


This document was generated automatically. Subject to technical changes and errors. Distribution as well as duplication of this document, its utilisation and communication of its content only permitted with express consert.






Grip range

Defines the range of total thickness of the customers part (even if it consists of more than one layer)



Hole geometry If round -> diameter If hexagonal -> wigth across flats



Head projection after setting

Variable according to the application (setting load, material substrate, etc.)

Blind side projection after installation

Defines the clearance needed on the blind side (cannot be used for quality control)

Setting stroke

Difference of total length before and after installation



in accordance to chosen RIVKLE®



All technical data refer to the measure mm

Böllhoff Group • Archimedesstr. 1-4 • 33649 Bielefeld • Phone: +49 521 4482-1387 • fat@boellhoff.com • eshop.boellhoff.de/en/home This document was generated automatically. Subject to technical changes and errors. Distribution as well as duplication of this document, its utilisation and communication of its content only permitted with express consert.