# All technical data refer to the measure mm

# **RIVKLE® SFC Standard blind rivet nuts**


Steel zinc-plated | Plain | Cylindrical


Note: Thread according to ISO 6h (ISO 68-1) - Corrosion resistance 400 h salt spray

Technical information can be found on the last page.




Diameter	Article number	Drilling diameter d		Е	L <sub>2</sub>	е		Length (I)	
(d)		nominal size	В	nominal size		min.	max.	nominal size	N
M 6	23391060968	9.1	13	1.5	11	2.0	3.5	20.7	12000
	23391060969		18			2.0	3.5	20.7	
	23391060970		18			3.5	5.0	22.2	
	23391060971		13			3.5	5.0	22.2	
M 8	23391080848	11.1	20	1.5	12	2.0	3.5	22.0	18000
	23391080849		20			3.5	5.0	23.5	






### **Grip range**

Defines the range of total thickness of the customers part (even if it consists of more than one layer)



## Hole geometry

If round -> diameter If hexagonal -> wigth across flats



Difference of total length before and after installation



\*in accordance to chosen RIVKLE®\*

