

## QUICKLOC® Locking bolts



Article number	Colour	Max. cover height	Functional length	Grip	
				length receptacle size 1	length receptacle size 2
06600000001	black	3.6	16.2	5.3	4.3
06600000004	silver	0.9	15.3	4.4	3.4
06600000016	black	15.1	–	16.8	15.8
06600000019	black	3.2	19.7	4.9	3.9
06600000020	grey	3.2	23.3	4.9	3.9
06600000022	black	13.1	25.7	14.8	13.8
06600000023	white	4.6	17.2	6.3	5.3
06600000024	black	28.9	41.5	28.4	27.4
06601065317	black	2.2	14.6	3.9	2.9
06601065318	black	2.7	15.3	4.4	3.4
06601065319	black	4.0	16.6	5.7	4.7
06601065320	black	4.0	16.2	5.7	4.7
06601065321	black	4.0	16.6	5.7	4.7
06601065329	black	12.4	25.0	14.1	13.1
06601075318	black	2.7	15.3	4.4	3.4
06601075320	black	2.7	15.3	4.4	3.4
06601075323	black	7.9	20.5	9.6	8.6
06601105320	black	3.4	16.0	5.1	4.1
06601345218	white	2.0	13.5	2.6	1.6
06601345923	grey	2.2	19.1	8.2	7.2
06601405333	black	–	–	18.2	17.2
06601515319	black	2.7	15.3	4.4	3.4
06601525245	white	18.5	41.0	30.1	29.1
06601525318	black	2.7	15.3	4.4	3.4
06601525323	black	6.5	19.1	8.2	7.2
06601525324	black	7.9	20.5	9.6	8.6
06601535347	black	28.4	44.2	33.3	32.3
06601575320	black	3.2	15.8	4.9	3.9
06611455338	black	2.6	30.0	19.1	18.1
06611515323	black	2.7	15.3	4.4	3.4
06611605322	black	1.7	14.3	3.4	2.4

All technical data refer to the measure mm



## QUICKLOC® Locking bolts

Article number	Head diameter	Head height	Shank diameter	Closing curve	Force application
06600000001	25.0	3.0	5	7/3	Raised head
06600000004	17.0	9.0	7	7/5	Handle
06600000016	16.0	3.5	5	7/3	Coin slot
06600000019	25.3	12.2	5	7/3	Handle
06600000020	25.3	12.2	5	7/5	Handle
06600000022	19.0	12.0	5	7/3	Handle
06600000023	19.0	12.5	5	7/2	Handle
06600000024	19.0	14.3	5	7/3	Handle
06601065317	25.0	7.0	5	7/3	Handle
06601065318	25.0	7.0	5	7/2	Handle
06601065319	25.0	7.0	5	7/2	Handle
06601065320	25.0	12.2	5	7/3	Handle
06601065321	25.0	7.0	5	7/3	Handle
06601065329	25.0	7.0	5	7/3	Handle
06601075318	17.0	7.0	5	7/2	Handle
06601075320	17.0	7.0	5	7/3	Handle
06601075323	17.0	7.0	5	7/1	Handle
06601105320	19.0	12.0	5	7/3	Handle
06601345218	11.0	3.8	7	7/4	Cross recess
06601345923	11.0	3.8	7	7/3	Slotted
06601405333	16.0	4.0	7	7/3	Coin slot
06601515319	13.0	5.0	5	7/3	Slotted
06601525245	19.0	3.0	7	7/3	Raised head
06601525318	19.0	3.0	5	7/2	Raised head
06601525323	19.0	3.0	5	7/3	Raised head
06601525324	19.0	3.5	5	7/3	Raised head
06601535347	11.0	3.8	7	7/2	Slotted
06601575320	14.2	5.0	5	7/3	Hexalobular / Torx
06611455338	16.0	4.7	7	7/5	Cross recess
06611515323	13.0	5.0	5	7/5	Slotted
06611605322	16.0	2.3	5	7/5	Cross recess

All technical data refer to the measure mm

