


B 3017
Hose clamps

Version: W4

Stainless steel 1.4301 | Cr(VI)-free

Further information: Version W4: All parts made of stainless steel 1.4301



Diameter (d)	b ₁			b ₂	h ₁ max.	h ₂		
	min.	max.	nominal size			max.	nominal size	min.
8-16	8	10	9	14	14	9	8	7
12-22	8	10	9	14	14	9	8	7
16-27	8	10	9	14	14	9	8	7
	11	13	12	20	16			
20-32	8	10	9	14	14	9	8	7
	11	13	12	20	16			
25-40	8	10	9	14	14	9	8	7
	11	13	12	20	16			
30-45	8	10	9	14	14	9	8	7
	11	13	12	20	16			
32-50	8	10	9	14	14	9	8	7
35-50	11	13	12	20	16	9	8	7
40-60	8	10	9	14	14	9	8	7
	11	13	12	20	16			
50-70	8	10	9	14	14	9	8	7
	11	13	12	20	16			
60-80	8	10	9	14	14	9	8	7
	11	13	12	20	16			
70-90	8	10	9	14	14	9	8	7
	11	13	12	20	16			
80-100	8	10	9	14	14	9	8	7
	11	13	12	20	16			
90-110	8	10	9	14	14	9	8	7
	11	13	12	20	16			
100-120	11	13	12	20	16	9	8	7
110-130	11	13	12	20	16	9	8	7
120-140	11	13	12	20	16	9	8	7
130-150	11	13	12	20	16	9	8	7
140-160	11	13	12	20	16	9	8	7
150-170	11	13	12	20	16	9	8	7
160-180	11	13	12	20	16	9	8	7
170-190	11	13	12	20	16	9	8	7

All technical data refer to the measure mm



B 3017

Hose clamps

Version: W4

Stainless steel 1.4301 | Cr(VI)-free

Diameter (d)	h ₃ min.	n			s			s ₁
		nominal size	min.	max.	nominal size	min.	max.	
8-16	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
12-22	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
16-27	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
20-32	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
25-40	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
30-45	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
32-50	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
35-50	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
40-60	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
50-70	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
60-80	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
70-90	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
80-100	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
90-110	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
100-120	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
110-130	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
120-140	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
130-150	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
140-160	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
150-170	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
160-180	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7
170-190	4	1.2	1.16	1.53	0.7	0.5	0.9	0.7

All technical data refer to the measure mm

