


DIN 439 similar to ISO 4035

Hexagon nuts

Low version | Form B: with chamfer

Stainless steel A2 | Cr(VI)-free | Metric thread

Further information: DIN-standard has been withdrawn | different spanner widths for M10, M12, M14 and M22 | only the regular thread is included in ISO 4035 | the fine thread was transferred to ISO 8675



Diameter (d)	da		dw	e	m		s		Pitch (P)	Tool size
	min.	max.			min.	max.	min.	max.		
M1.6	1.6	1.84	2.4	3.48	0.75	1.0	3.08	3.2	0.35	SW 3,2
M2	2.0	2.30	3.1	4.32	0.95	1.2	3.82	4.0	0.40	SW 4
M2.5	2.5	2.90	4.1	5.45	1.35	1.6	4.82	5.0	0.45	SW 5
M3	3.0	3.45	4.6	6.01	1.55	1.8	5.32	5.5	0.50	SW 5,5
M4	4.0	4.60	5.9	7.66	1.95	2.2	6.78	7.0	0.70	SW 7
M5	5.0	5.75	6.9	8.79	2.45	2.7	7.78	8.0	0.80	SW 8
M6	6.0	6.75	8.9	11.05	2.90	3.2	9.78	10.0	1.00	SW 10
M8	8.0	8.75	11.6	14.38	3.70	4.0	12.73	13.0	1.25	SW 13
M10	10.0	10.80	15.6	18.90	4.70	5.0	16.73	17.0	1.50	SW 17
M12	12.0	13.00	17.4	21.10	5.70	6.0	18.67	19.0	1.75	SW 19
M14	14.0	15.10	20.5	24.49	6.42	7.0	21.67	22.0	2.00	SW 22
M16	16.0	17.30	22.5	26.75	7.42	8.0	23.67	24.0	2.00	SW 24
M18	18.0	19.50	24.9	29.56	8.42	9.0	26.16	27.0	2.50	SW 27
M20	20.0	21.60	27.7	32.95	9.10	10.0	29.16	30.0	2.50	SW 30
M22	22.0	23.80	29.5	35.03	9.90	11.0	31.00	32.0	2.50	SW 32
M24	24.0	25.90	33.2	39.55	10.90	12.0	35.00	36.0	3.00	SW 36
M27	27.0	29.20	38.0	45.20	12.40	13.5	40.00	41.0	3.00	SW 41
M30	30.0	32.40	42.7	50.85	13.90	15.0	45.00	46.0	3.50	SW 46
M33	33.0	35.60	46.6	55.37	15.40	16.5	49.00	50.0	3.50	SW 50
M36	36.0	38.90	51.1	60.79	16.90	18.0	53.80	55.0	4.00	SW 55
M39	39.0	42.10	55.9	66.44	18.20	19.5	58.80	60.0	4.00	SW 60

All technical data refer to the measure mm

