


**DIN 439** similar to ISO 4035

## Hexagon nuts

Low version | Form B: with chamfer

Brass | nickel plated | Cr(VI)-free | Metric thread

Further information: DIN-standard has been withdrawn | different spanner widths for M10, M12, M14 and M22 | only the regular thread is included in ISO 4035 | the fine thread was transferred to ISO 8675



| Diameter<br>(d) | da   |       | dw   | e     | m    |      | s     |      | Pitch<br>(P) | Tool<br>size |
|-----------------|------|-------|------|-------|------|------|-------|------|--------------|--------------|
|                 | min. | max.  |      |       | min. | max. | min.  | max. |              |              |
| M3              | 3    | 3.45  | 4.6  | 6.01  | 1.55 | 1.8  | 5.32  | 5.5  | 0.50         | SW 5,5       |
| M4              | 4    | 4.60  | 5.9  | 7.66  | 1.95 | 2.2  | 6.78  | 7.0  | 0.70         | SW 7         |
| M5              | 5    | 5.75  | 6.9  | 8.79  | 2.45 | 2.7  | 7.78  | 8.0  | 0.80         | SW 8         |
| M6              | 6    | 6.75  | 8.9  | 11.05 | 2.90 | 3.2  | 9.78  | 10.0 | 1.00         | SW 10        |
| M8              | 8    | 8.75  | 11.6 | 14.38 | 3.70 | 4.0  | 12.73 | 13.0 | 1.25         | SW 13        |
| M10             | 10   | 10.80 | 15.6 | 18.90 | 4.70 | 5.0  | 16.73 | 17.0 | 1.50         | SW 17        |
| M12             | 12   | 13.00 | 17.4 | 21.10 | 5.70 | 6.0  | 18.67 | 19.0 | 1.75         | SW 19        |
| M16             | 16   | 17.30 | 22.5 | 26.75 | 7.42 | 8.0  | 23.67 | 24.0 | 2.00         | SW 24        |

All technical data refer to the measure mm

