

DIN 939
Studs


Threaded end $\approx 1,25 d$

Stainless steel A2 | Cr(VI)-free | Metric thread



Einschraubende

Mutterende



Diameter (d)	b			b ₁ nominal size	Pitch (P)	z ₂	z ₁
	l up to 125	l up to 200	l longer than 200				
M5	16	22	–	6.5	0.80	1.00	2
M6	18	24	–	7.5	1.00	1.25	2.5
M8	22	28	–	10.0	1.25	1.60	3.2
M10	26	32	45	12.0	1.50	1.90	3.8
M12	30	36	49	15.0	1.75	2.20	4.3
M16	38	44	57	20.0	2.00	2.50	5
M20	46	52	65	25.0	2.50	3.20	6.3
M24	54	60	73	30.0	3.00	3.80	7.5
M27	60	66	79	35.0	3.00	3.80	7.5
M30	66	72	85	38.0	3.50	4.50	9

nominal size	Length (l)	
	min.	max.
25	24.58	25.42
30	29.58	30.42
35	34.50	35.50
40	39.50	40.50
45	44.50	45.50
50	49.50	50.50

nominal size	Length (l)	
	min.	max.
55	54.40	55.60
60	59.40	60.60
65	64.40	65.60
70	69.40	70.60
75	74.40	75.60
80	79.40	80.60

nominal size	Length (l)	
	min.	max.
85	84.30	85.70
90	89.30	90.70
95	94.30	95.70
100	99.30	100.70
110	109.30	110.70
120	119.30	120.70

All technical data refer to the measure mm



DIN 939
Studs

Threaded end $\approx 1,25 d$

Stainless steel A2 | Cr(VI)-free | Metric thread

Diameter (d)	Length (l)																	
	25	30	35	40	45	50	55	60	65	70	75	80	85	90	95	100	110	120
M5	●	●	●	●	●	●												
M6	●	●		●	●	●	●	●										
M8		●	●	●	●	●				●	●							
M10			●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
M12				●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
M16				●		●	●	●	●	●	●	●	●	●	●	●	●	●
M20					●				●	●	●	●	●	●	●	●	●	●
M24										●			●	●	●	●	●	●
M27										●		●		●		●	●	●
M30														●		●	●	●

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

