

## HELICOIL® Plus prewinder

for HELICOIL® pneumatic and electrical installation tool P-PSG 256 | E-PSG 256

Leader cartridge for HELICOIL® installation tools to process HELICOIL® Plus Free Running and HELICOIL® Plus Screwlock thread inserts.

**Suited for:**

- P-PSG 256 pneumatic installation tool
- E-PSG 256 electrical installation tool

Technical information can be found on the last page.



Diameter (d)	Article number	Pitch (P)
UNC 1/4"-20	01602774632	1.27
UNF 1/4"-28	01601774732	0.91
UNC 2-56	01602763632	0.43
M 2.5	01601725032	0.45
M 3	01601703032	0.50
M 4	01601704032	0.70
UNC 4-40	01601765632	0.63
UNF 4-48	01601765732	0.53
M 5	01601705032	0.80
M 6	01601706032	1.00
UNC 6-32	01601767632	0.79
UNF 6-40	01601767732	0.63
UNC 8-32	01601768632	0.79
UNF 8-36	01601768732	0.71
UNC 10-24	01601769632	1.05
UNF 10-32	01602769732	0.79

All technical data refer to the measure mm



## HELICOIL® Plus thread inserts





W and  $d_1$  are the control values for thread inserts (Free Running and Screwlock) before they have been installed. The length can only be measured for installed thread inserts.

### Holding thread



### Assembly



tang not broken off

Prior to tapping, counter-bore 90° and deburr.  
Outside diameter of countersink =  $D_{HC} + 0.1 \text{ mm}$ .

- d = Nominal thread diameter
- P = Thread pitch
- $d_1$  = Outside diameter of thread insert prior to installation
- W = Number of threads prior to installation
- $D_{HC}$  = Outside diameter of the parent thread
- $D_{1HC}$  = Crest diameter
- B = Suitable twist drill diameter. Please note:  $D_{1HC}$  is critical for selecting the correct twist drill diameter.
- $t_1$  = Minimum depth of tapped hole according to DIN 76 – Part 1 (guide value)
- $t_2$  = The nominal length of the thread insert corresponds to the minimum length of the full parent thread for blind holes or the minimum plate thickness for a through hole.
- $t_3$  = Maximum screw-in depth when the tang is not removed
- $t_5$  = Distance of the thread insert from the joint face = 0.25 to 0.5 P, if  $t_2$  corresponds to the above-mentioned minimum value

When you use HELICOIL® Plus thread inserts for volume production, we recommend to add at least  $1 \times P$  to values  $t_1$  and  $t_2$ .

All technical data refer to the measure mm

