All technical data refer to the measure mm

RIVKLE® Standard blind rivet nuts


Stainless Steel A4 | Flat head | Plain | Cylindrical | Open


Note: RIVKLE $^{\otimes}$ produced in stainless steel A4 providing the best corrosion resistance | Thread according to ISO 6h (ISO 68-1)

Technical information can be found on the last page.




Diameter	Article number	Drilling diameter d		Е	L ₂	е		Length (I)	
(d)		nominal size	В	nominal size		min.	max.	nominal size	N
M 4	23304040020	6	9	1	7.5	0.5	2	12.0	9500
M 5	23304050030	7	10	1	7.5	0.5	3	12.5	12000
M 6	23304060030	9	12	1.5	10.0	0.5	3	16.0	15000
M 8	23304080030	11	15	1.5	11.2	0.5	3	17.5	20000






Grip range

Defines the range of total thickness of the customers part (even if it consists of more than one layer)




Hole geometry

If round -> diameter If hexagonal -> wigth across flats



Difference of total length before and after installation



in accordance to chosen RIVKLE®

