All technical data refer to the measure mm


RIVKLE® Mandrel


Spare threaded mandrel for the RIVKLE® P3007 pneumatic/hydraulic setting tool to process RIVKLE® Standard blind rivet nuts.

- Threaded mandrel, for series production
- Hardened metal alloy
- Thread as per ISO 6H (ISO 68-1)

Technical information can be found on the last page.


Diameter	Article number	For
(d)		tool type
M 8	23615908020	P3007
M 10	23615910020	P3007
M 12	23615912020	P3007
M 14	23615914020	P3007
M 16	23615016020	P3007






Grip range

Defines the range of total thickness of the customers part (even if it consists of more than one layer)




Hole geometry

If round -> diameter If hexagonal -> wigth across flats



Difference of total length before and after installation



in accordance to chosen RIVKLE®

