# All technical data refer to the measure mm

# **RIVKLE®** Standard blind rivet studs


Steel zinc-plated | Flat head | Knurled | Cylindrical


Note: Thread according to ISO 6h (ISO 68-1) - Corrosion resistance 400 h salt spray

Technical information can be found on the last page.




Diameter	Article number	Drilling diameter d		Е	L <sub>1</sub>	L <sub>2</sub>	е				
(d)		nominal size	В	nominal size			min.	max.	S	min.	max.
M 5	37227050110	7	10	1	11.2	5.0	0.5	3	S = 5.0 - e	7.5	12.0
	37227050115									12.5	17.0
	37227050120									17.5	22.0
	37227050125									22.5	27.0
M 6	37227060115	9	13	1.5	14.2	8.5	0.5	3	S = 5.2 - e	14.0	18.5
	37227060120									19.0	23.5
	37227060125									24.0	28.5
M 8	37227080115	11	16	1.5	15.6	8.5	0.5	3	S = 5.7 - e	13.5	18.0
	37227080120									18.5	23.0
	37227080125									23.5	28.0






### **Grip range**

Defines the range of total thickness of the customers part (even if it consists of more than one layer)




## Hole geometry

If round -> diameter If hexagonal -> wigth across flats



Difference of total length before and after installation



\*in accordance to chosen RIVKLE®\*

