# All technical data refer to the measure mm

# RIVKLE® BRK 01 Kit

RIVKLE® kit including RIVKLE® BRK 01 hand-held setting pliers

## **Delivery scope:**

- 1 RIVKLE® BRK 01 hand-held setting pliers
- 4 threaded mandrels and 4 anvils (M3, M4, M5, M6)
- 50 blind rivet nuts each, small countersunk head, steel (M3, M4, M5, M6)
- Practical case for storage and transport
- Operating instructions

### **Function:**


Screwing and unscrewing of the RIVKLE® blind rivet nut using a knurled nut. Setting is performed through the lever action of the hand-held tool.


Technical information can be found on the last page.



Diameter	Article number	Weight
(d)		g


M3 - M6 23511900501 600






### **Grip range**

Defines the range of total thickness of the customers part (even if it consists of more than one layer)



### Hole geometry

If round -> diameter If hexagonal -> wigth across flats



Difference of total length before and after installation



\*in accordance to chosen RIVKLE®\*

